

# Carestream NDT

## INDUSTREX Photochemicals for Automatic and Manual Processing

High chemical stability – includes consistent image quality over an extended period of time. Great with automatic and manual processing, providing consistent image quality and ease of use.



High Stability.  
Consistent Results.



# INDUSTREX Photochemicals for Automatic and Manual Processing



## INDUSTREX Single Part Developer Replenisher 2x20L

Ideal for 5-minute automatic or 4-minute manual cycles for processing of all NDT films. Single Part Developer Replenisher is an all-in-one developer and replenisher; it is only necessary to add water to the proper dilution. Single part concentrate dilutes 1+3 w/H<sub>2</sub>O.

- Designed for use in automatic and manual processing
- Low replenishment rates for efficient use of photochemicals
- High chemical stability for image quality over time, resistant to aerial oxidation,
- Strengthened "activation power" allows for fast processing and high productivity
- Outstanding, consistent image quality — cold (blue) image "tone" and low granularity
- Can be used in chemical auto mixers

INDUSTREX Single Part Developer Replenisher

Catalog Number 5315288



## INDUSTREX LO Fixer and Replenisher 2x20L

Recommended for all NDT and industrial imaging films. Great for automatic and manual processing, can be used in chemical auto mixers. Single part concentrate dilutes 1+3 w/H<sub>2</sub>O.

- Designed for use in automatic and manual processing
- Low replenishment rates for efficient use of photochemicals
- Archival Performance Characteristics
- Low Odor

INDUSTREX LO Fixer and Replenisher

Catalog Number 5159082

## Accessory Chemicals for Manual Processing



## INDUSTREX Manual Stop Bath

1L bottle of single part concentrate when mixed provides 20L of working strength stop bath solution used in manual processing applications. Manual Stop Bath is odorless and contains a color indicator that turns color at pH 5.2 from orange-yellow to magenta/red when exhausted. Single part concentrate dilutes 1+19 w/H<sub>2</sub>O.

INDUSTREX Manual Stop Bath 1X1L. To make 20L.

Catalog Number 1054873



## INDUSTREX Manual Rinse Solution

1L bottle of single part concentrate when mixed provides 20L of working strength rinsing solution used in manual processing applications. Manual Rinse Solution is a wetting agent that effectively reduces water spots and drying marks on film. Single part concentrate dilutes 1+19 w/H<sub>2</sub>O.

INDUSTREX Manual Rinse Solution 1X1L. To make 20L.

Catalog Number 1057025

[carestream.com/ndt](http://carestream.com/ndt)

**CARESTREAM NDT AND YOU.  
WE'RE BETTER TOGETHER.**



**Carestream**